

P.O. BOX 265
OGDENSBURG, NY
U.S.A. 13669-0265
TEL: (315) 472-5270
FAX: (613) 226-2802

AVTECH ELECTROSYSTEMS LTD.

NANOSECOND WAVEFORM ELECTRONICS SINCE 1975

TEL: 1-800-265-6681 FAX: 1-800-561-1970 U.S.A. & CANADA

e-mail: info@avtechpulse.com

BOX 5120 STN. F OTTAWA, ONTARIO CANADA K2C 3H4 TEL: (613) 226-5772 FAX: (613) 226-2802

INSTRUCTIONS


MODEL AVO-9C-C-IBM2A PULSE GENERATOR MODEL AVX-S1-IBM2A OUTPUT MODULE

S.N.:

WARRANTY

Avtech Electrosystems Ltd. warrants products of its manufacture to be free from defects in material and workmanship under conditions of normal use. If, within one year after delivery to the original owner, and after prepaid return by the original owner, this Avtech product is found to be defective, Avtech shall at its option repair or replace This warranty does not apply to units said defective item. which have been dissembled, modified or subjected to conditions exceeding the applicable specifications or ratings. This warranty is the extent of the obligation or liability assumed by Avtech with respect to this product and no other warranty or guarantee is either expressed or implied.

Fig. 1 PULSE GENERATOR TEST ARRANGEMENT



(AVX-S1 MODULE REMOVED)

Notes:

- The bandwidth capability of components and instruments used to display the pulse generator output signal (attenuators, cables, connectors, etc.) should exceed 5 gigahertz.
- 2) The use of 40 dB attenuator at the sampling scope vertical input channel will insure a peak input signal to the sampling scope of less than one Volt.
- 3) The TRIG output channel provides a TTL 100 ns pulse (to 50 Ohms).
- 4) To obtain a stable output display the PRF control on the front panel should be set mid-range while the PRF range switch may be in either range. The front panel TRIG toggle switch should be in the INT position. The front panel DELAY control and the scope triggering controls are then adjusted to obtain a stable output. It is recommended that the DELAY control first be set max counter clockwise and then turned clockwise until a stable display is obtained. The scope may then be used to set the desired PRF by rotating the PRF control and by means of the PRF range switch.
- 5) The output pulse width is controlled by means of the front panel one turn PW control. The control should initially be set maximum clockwise and the pulse width adjusted using an oscilloscope. Rotation of the PW pot causes the position of the falling edge of the pulse to change. <u>CAUTION</u>: The output pulse width is PRFdependent and so the PW reading given by the dial will not be valid at all PRF settings.
- 6) The output pulse amplitude is controlled by means of the front panel one turn AMP control.
- 7) An external clock may be used to control the output PRF of the unit by setting the front panel TRIG toggle switch in the EXT position and applying a 10 ns (or wider) TTL level pulse to the TRIG BNC connector input. The AVO-9C unit triggers on the rising edge of the input trigger pulse. For operation in this mode, the scope time base must also be triggered by the external clock rather than from the TRIG output.
- 8) <u>WARNING</u>: Model AVO-9C-C may fail if triggered at a PRF greater than 1.0 MHz.
- 9) The Model AVO-9C-C pulse generator can withstand an infinite VSWR on the output port.

- 10) The AVO-9C-C unit can be converted from 110 to 220V 50-60 Hz operation by adjusting the voltage selector card in the rear panel fused voltage selector-cable connector assembly.
- 11) For additional assistance:

Tel:	(613)	226-5772
Fax:	(613)	226-2802

PULSE GENERATOR TEST ARRANGEMENT

(AVX-S1 MODULE CONNECTED)





Fig. 2

.


- 1) A general description of the AVX-S1 module is given in the enclosed data sheet.
- 2) The AVX-S1 module should be connected to the AVO-9C-C mainframe via the supplied 24" RG174 cable. The diode current may be monitored by connecting the MI output port to the sampling scope via a 20 dB attenuator. The output amplitude ($V_{\rm MI}$, Volts) and diode current ($I_{\rm D}$, Amp) are related as follows:

$$I_{D} = 0.2 (V_{MI})$$

- 3) The laser diode plugs directly into the socket on the side of the AVX-S1 module.
- 4) A forward DC bias may be applied to the laser diode by connecting a DC potential of 0 to -5 Volts to the DC solder terminal. The application of a small forward bias often yields a more ideal diode current waveform (as observed on the MI port). Note that the DC port must be shorted to ground if a bias is not applied.
- 5) The photo diode cathode is connected to PIN 4 of the AMPHENOL 57-60140 D connector while the photo diode anode is connected to PIN 5. PIN 1 of the D connector is connected to ground.







The AVX-S series of bias insertion units is designed for applying pulse or RF CW signals and DC bias to laser diodes which insert into a high quality socket included on the mount. The bias insertion module includes the necessary networks to match the laser diode to the pulse or RF source as well as networks for applying DC bias to the diode. Optional outputs allow for monitoring of the laser diode current, voltage and a photo detector diode output. Readily available socket configurations (TO-18, TO-5, TO-3, OP-3) are shown on the following page. Note that the laser diodes are not supplied with the AVX-S series.

The AVX-S series includes 3 basic models namely the AVX-S1, AVX-S2 and the AVX-S3. The basic functional equivalent circuit for the three models are shown below. Model AVX-S1 is specifically designed for ultra high-speed, low current applications (rise times as low as 200 psec, bandwidths to 1 GHz, I <1.0 ampere). Model AVX-S1 is employed in the AVO-9-C series of diode drivers. Model AVX-S2 is intended for application with rise times greater than 2 nsec and currents above 1 ampere. Model AVX-S3 is specifically designed for use with the AVO-2 and AVO-5 series pulse generators (which provide currents in the range of 5 to 50 amperes).


The input series blocking capacitor in Models AVX-S1 and AVX-S2 presents a low impedance to RF CW signals and to baseband pulses while the shunt indicator presents a high impedance to RF (or pulse) signals but an extremely low impedance to the DC bias. The resistor in series with the laser diode is selected to insure that the impedance at the IN port is 50 ohms. Normally a laser diode resistance of 3 ohms is assumed.

The optional diode current monitor (MI) provides an output waveform (to 50 ohms) which is an attenuated replica of the laser diode current. The output amplitude (VMI, volts) and diode current (ID, Amps) are related as follows:

-S1:
$$I_D = 0.2V_{MI}$$
 -S2: $I_D = V_{MI}$

The optional diode voltage monitor (MV) provides an output waveform that may be related to the voltage across the laser diode (VD, voits) as follows:

-S1:
$$V_D = 10 (V_{MV} - V_{MI}) - S2: V_D = 10 V_{MV}$$



- Socket mounting of laser diodes
- Peak currents from 100 mA to 48 Amos
- Pulse widths from 0.4 to 200 nsec
- Rise times from 0.2 to 2.0 nsec
- Pulse or CW RF
- Diode current and voltage monitor options

Model AVX-S3 is available in four different versions (AVX-S3A, AVX-S3B, AVX-S3C and AVX-S3D) all of which include a matching transformer which effectively boosts the laser diode current beyond that provided by the pulse source.

Model AVX-S3A is designed to match 50 ohm pulse generators such as Model AVO-2-C to 12 ohm loads with peak currents of 5 amperes. Consequently, the resistor Ag in the equivalent circuit for this model is 10 ohm. This resistor is accessible in all AVX-S3 models and may be changed by the user (by desoldering). The series resistance of the laser diode and the resistor β_S must equal the pulse generator source impedance divided by N². Consequently, if the series resistance of the laser diode is relatively high, it then may be necessary to reduce the value of Rg. Model AVX-S3B is designed to match 50 ohm pulse generators such as Model AVO-5-C to 3 ohms and will provide peak diode currents up to 28 amperes. Model AVX-S3C is designed to match Models AVO-2W-C and AVO-2-C (25 ohm source impedance) to load resistance of about 5 ohms and will provide peak diode currents as high as 10 amperes. Model AVX-S3D is designed for use with Model AVO-5B-C and will provide up to 48 amperes of diode current.

Two optional SMA output connectors provide attenuated coincident replicas of the diode current (-MI option) and diode voltage (-MV option) as per the following relationships (Amps, Volts):


$$I_D = -\frac{10 V_{MI}}{R_S}$$
 $V_D = 10 (V_{MV} - V_{MI})$

All AVX-S3 units include two foot long input cables with SMA male connectors.


When ordering members of the AVX-S family, the customer must specify the basic model number (eg. AVX-S1) and the following additional information.


- Diode package type (eg. TO-18) and the required pin conneca) tions (eg. anode, cathode, ground etc). See the following page for readily available package mounting. Contact Avtech for special or different packages.
- b) Desired options (eg. -MI, -MV, -MD),

Contact Avtech for your special requirements.




Moael:	AVX-S1	AVX-S2	AVX-S3A	AVX-S3B	AVX-S3C	AVX-S3D
Peak dioge current:	400 mA	2 Amps	5 Amps	28 Amps	10 Amps	48 Amps
Max. input amplitude:	20 volts	100 voits	150 volts	350 volts	150 volts	150 volts
Pulse width (nsec):	0.4 - 200	1 - 1000	2 - 100	2 - 100	2 - 100	5 - 500
Rise time insec):	0.2	0.5	0.5	1.0	0.5	2.0
Pulse PRF range:	DC - 0.5 GHz	DC - 100 MHz	DC - 10 MHz	DC-10 MHz	DC - 10 MHz	DC - 1 MHz
CW frequency range:	10 MHz - 1.0 GHz	1 - 200 MHz	•	•	•	•
Max. bias current:	100 mA	100 mA	100 mA	100 mA	100 mA	100 mA
Max. bias voitage:	50 voits	50 volts	50 voits	50 volts	50 volts	50 voits
Input imcedance:	50 ohms	50 onms	50 ohms	50 ohms	25 ohms	12 ohms
N:	•	-	2	4	2	4
Rs (ohms):	•	•	10	3	5	0.7
IN connector:	SMA					
Monitor connector:	SMA					
Bias connector:	Solder pin					
Size (in):		1.6 x 2.6 x 3.0				
Materiai:		Cast aluminum, blue enamel				
Mounting:	Any					






AVX-S1 FUNCTIONAL EQUIVALENT CIRCUIT



AVX-S2 FUNCTIONAL EQUIVALENT CIRCUIT




AVX-S3 INPUT ASSEMBLY (FOR OP-3 PACKAGE)

AVX-S3 FUNCTIONAL EQUIVALENT CIRCUIT




Π

50.45







TYPICAL PACKAGES

TO-3 8 PIN PIN CIRCLE DIA 500±.050* 12.7±1.27mm 40 1 01* MAX 80° TY E 156±.005" 3.96±0.13mm OIA 2 HOLES 1 187±.01° 30.20±0.25mm Bon Vie




Fig. 3

FRONT PANEL CONTROLS

J.


- (1) <u>ON-OFF Switch</u>. Applies basic prime power to all stages.
- (2) <u>PRF Control</u>. The PRF RANGE and PRF controls determine output PRF as follows:

		PRF	MIN	PRF	MAX
Range	1	100	Hz	1	kHz
Range	2	1	kHz	10	kHz
Range	3	10	kHz	100	kHz
Range	4	100	kHz	1	MHz

- (3) <u>DELAY Controls</u>. Controls the relative delay between the reference output pulse provided at the TRIG output (4) and the main output (7). This delay is variable over the range of 0 to at least 500 ns.
- (4) <u>TRIG Output</u>. This output precedes the main output (7) and is used to trigger the sampling scope time base. The output is a TTL level 100 ns (approx) pulse capable of driving a fifty Ohm load.
- (5) <u>PW Control</u>. A one turn control which varies the output pulse width from 1 to 10 ns.
- (6) <u>AMP Control</u>. A one turn control which varies the output pulse amplitude from 0 to 7 V to a fifty Ohm load.
- (7) <u>OUT</u>. SMA connector provides output to 50 Ohms.
- (8) <u>EXT-INT Control</u>. With this toggle switch in the INT position, the PRF of the AVO-9C unit is controlled via an internal clock which in turn is controlled by the PRF controls. With the toggle switch in the EXT position, the AVO-9C unit requires a 50 ns (or wider) TTL level pulse applied at the TRIG input in order to trigger the output stages. In addition, in this mode, the scope time base must be triggered by the external trigger source.

Fig. 4

BACK PANEL CONTROLS




e

÷

(1) <u>FUSED CONNECTOR, VOLTAGE SELECTOR</u>. The detachable power cord is connected at this point. In addition, the removable cord is adjusted to select the desired input operating voltage. The unit also contains the main power fuse (0.5 A SB). Fig. 5

SYSTEM BLOCK DIAGRAM





AVTECH ELECTROSYSTEMS LTD.

NANOSECOND WAVEFORM ELECTRONICS SINCE 1975

P.O. BOX 265
OGDENSBURG, NY
U.S.A. 13669-0265
TEL: (315) 472-5270
FAX: (613) 226-2802

TEL: 1-800-265-6681 FAX: 1-800-561-1970

e-mail: info@avtechpulse.com http://www.avtechpulse.com P.O. BOX 5120 STN. F OTTAWA, ONTARIO CANADA K2C 3H4 TEL: (613) 226-5772 FAX: (613) 226-2802

February 19, 1997.

Bill Risk IBM Almaden Research Center 650 Harry Road Dept. K10/80 San Jose, CA 95120-6099

Tel: 408-927-2467 Fax: 408-927-2100

Dear Bill:

Following your FAX of February 14th, I am pleased to provide the following revised price and delivery quotations:

A) Model designation: AVO-9C-C-N-IBM1A. (as AVO-9C-C-N-IBM1 but AVX-S1 not included). Amplitude: 0 to 100 mA. Pulse width: 0.6 to 10 ns. Rise time: \leq 0.3 ns. Fall time: \leq 0.3 ns. PRF: 0 to 25 MHz. Price: \$4,234.00 US each, FOB destination. Delivery: 45-60 days ARO.

B)	Model designation:	AVX-S1-IBM1A.
		Output module configured to accept the 14 pin package (LC81-18). Compatible with Model AVO-9C-C-N-IBM1A. All pins (with the exception of pins 9 and 10) are accessible via a 14 pin D connector on the side of the chassis. The diode current can be monitored via an SMA connector which provides an attenuated coincident replica of the diode current.
	Price:	\$700.00 US each, FOB destination.
	Delivery:	45-60 days ARO.
C)	Model designation:	AVO-9C-C-N-IBM2A.
		(as AVO-9C-C-N-IBM2 but AVX-S1 not included).
	Amplitude:	0 to 100 mA.
	Pulse width:	0.6 to 10 ns.
	Rise time:	≤ 0.3 ns.
	Fall time:	≤ 0.3 ns.
	PRF:	0 to 1.0 MHz.
	Price:	\$4,234.00 US each, FOB destination.
	Delivery:	45-60 days ARO.

D) Model designation:

AVX-S1-IBM2A.

Output module configured to accept the 8 pin package (LCV75). Compatible with AVO-9C-C-N-IBM2A. All pins (with the exception of pins 6 and 7) are accessible via a 14 pin D connector on the side of the chassis. The diode current can be monitored via an SMA connector which provides an attenuated coincident replica of the diode current.

.../3

	Price: Delivery:	\$700.00 US each, FOB destination. 45-60 days ARO.
)	Model designation:	AVO-9C-C-N-IBM3A.
		(as AVO-9C-C-N-IBM3 but AVX-S1 not included).
	Amplitude:	0 to 100 mA.
	Pulse width:	0.6 to 10 ns.
	Rise time:	≤ 0.3 ns.
	Fall time:	≤ 0.3 ns.
]	PRF:	0 to 25 MHz.
1	Price:	\$4,234.00 US each, FOB destination.
Ľ	Delivery:	45-60 days ARO.

F) Model designation:

AVX-S1-IBM3A.

Output module configured to accept the Newport diode (part No ?). Compatible with AVO-9C-C-N-IBM3A. The diode current can be monitored via an SMA connector which provides an attenuated coincident replica of the diode current. - mnr

Price:

E)

\$550.00 US each, FOB destination.

Delivery:

45-60 days ARO.

Thank you for your continuing interest in our products. Please call me again (1-800-265-6681) if you require any additional information.

Yours truly, Buch

Dr. Walter Chudobiak Chief Engineer

WC:pr

May 21/97

Edition A

Disk: ANO-9 Mome: CCIBMZAA.INS