

AVTECH ELECTROSYSTEMS LTD.

NANOSECOND WAVEFORM ELECTRONICS SINCE 1975

info@avtechpulse.com http://www.avtechpulse.com/ Tel: 888-670-8729 (USA & Canada) or +1-613-686-6675 (Worldwide)


BOX 5120, LCD MERIVALE OTTAWA, CANADA K2C3H5

INSTRUCTIONS

MODEL AVX-S1-P1B OR AVX-S2-P1B
PLUG-IN SOCKET OUTPUT MODULE

SERIAL NUMBER: 14153

"P1B" SOCKET VIEW



WARRANTY

Avtech Electrosystems Ltd. warrants products of its manufacture to be free from defects in material and workmanship under conditions of normal use. If, within one year after delivery to the original owner, and after prepaid return by the original owner, this Avtech product is found to be defective, Avtech shall at its option repair or replace said defective item. This warranty does not apply to units which have been dissembled, modified or subjected to conditions exceeding the applicable specifications or ratings. This warranty is the extent of the obligation assumed by Avtech with respect to this product and no other warranty or guarantee is either expressed or implied.

TECHNICAL SUPPORT

Phone: 888-670-8729 (USA & Canada) or +1-613-686-6675 (Worldwide)

E-mail: info@avtechpulse.com World Wide Web: http://www.avtechpulse.com

TABLE OF CONTENTS


| WARRANTY | 2 |
|--|----|
| TECHNICAL SUPPORT | 2 |
| TABLE OF CONTENTS | 3 |
| INTRODUCTION | 4 |
| AVAILABLE OPTIONS | 5 |
| SPECIFICATIONS | 6 |
| GENERAL INFORMATION | 7 |
| INSTALLING THE DEVICE UNDER TEST | 7 |
| NORMAL TEST ARRANGEMENT | 8 |
| THERMAL CONTROL (-T1B and -T1D UNITS) | 9 |
| SIGNAL CONNECTORS ON THE OUTPUT MODULE | 10 |
| AMPLITUDE CONTROL | 10 |
| -INV OPTION | 11 |
| COMPATIBLE PULSE GENERATORS | 11 |
| PERFORMANCE CHECKSHEET | 12 |

Manual Reference: /fileserver2/officefiles/instructword/avx-s/AVX-S1-P1B,AVX-S2-P1B,ed10.odt. Last modified July 13, 2021.
Copyright © 2021 Avtech Electrosystems Ltd, All Rights Reserved.

INTRODUCTION

The AVX-S series of bias insertion units is designed to combine a pulse signal with a DC bias, and supply the resulting signal to a laser diode, which is inserted into a high quality socket included on the mount. The bias insertion module includes the necessary networks to match the laser diode to the pulse source, as well as networks for applying DC bias to the diode.

The AVX-S1-P1B and AVX-S2-P1B are specifically designed to accommodate butterfly-packaged laser diodes with the pinout illustrated below:



AVAILABLE OPTIONS

A number of options are available for the AVX-S1-P1B and AVX-S2-P1B, including:

-T1B option: Adds a secondary (low-bandwidth) slide-on socket board for pins 1-7 of

a butterfly package. A flexible cable connects the slide-on socket to the

output module. A male DB-9 connector is provided on the output module, which provides access to the thermal control pins of the diode.

DB-9 pin 2 connects to diode pin 2 (TH). DB-9 pin 3 connects to diode pin 5 (TH). DB-9 pin 4 connects to diode pin 1 (TEC+). DB-9 pin 5

connects to diode pin 14 (TEC-). The remaining DB-9 pins are unconnected. Pins 3, 4, 6, and 7 of the diode are grounded. Access to the photodiode, if present, is not provided. This option requires the -P1B option. This option is designed for compatibility with Thorlabs temperature controllers and Lumics laser diodes. It may be suitable for

others as well.

-T1D option: This is similar to the -T1B option, except DUT pins 3 and 4 are used for

the thermistor, instead of 2 and 5.

-INV option: Adds a polarity-inverting transformer to the input.

-RS33 option: Reduces RS from the standard value of 50 Ohms to 33 Ohms.

SPECIFICATIONS

| Model: | AVX-S1 | AVX-S2 |
|---|---|--------------------------------|
| Peak diode current (I _{PEAK}): | 400 mA | 2 Amps |
| Max. input amplitude: | 20 Volts | 100 Volts |
| Pulse width (PW): | 0.4 - 200 ns | 1 - 1000 ns |
| Rise time (20%-80%): | 0.2 ns | 0.5 ns |
| Pulse repetition freq. (PRF)4: | DC - 25 MHz | DC - 100 kHz |
| N (transformer ratio ^{1,2}): | +1 | |
| Rs ^{5,6} : | Standard: 50 Ω, ½ W With -RS33 option: 33 Ω, ½ W | 50 Ω, 5 W |
| Max. DC bias current: | 100 mA | |
| R_{DC} (in series with DC input) ⁷ : | 50 Ω, ½ W | |
| Max. DC bias voltage: | 50 Volts | |
| IN connector: | 1 SMA | |
| Included cables ³ : | 1 | |
| Other connectors: | MV, MI, MD: SMA (female), | DC bias: solder terminal |
| Diode socket: | The socket will accept pins 8-14 of a standard butterfly package with 0.5 mm wide pins. A pulse will be applied to the diode anode (pin 10). Pins 8-9 and 11-13 will be grounded. Pin 14 will be made accessible through a solder terminal. Four mounting holes on a 8.9 x 26 mm grid will be provided. The diode parasitic resistance (dV/dI at lasing) must be < 1 Ohm. | |
| Dimensions: | H x W x D: 42 mm x 67 mm | n x 76 mm (1.6" x 2.6" x 3.0") |
| Material: | Cast aluminum, blue enamel | |

¹⁾ The transformer reduces the input voltage by a factor of N (approx) and increases the current by a factor of N (approx). The load resistance

⁽R_s+R_{DIODE}) must equal 50Ω / N² (approx).

2) A polarity inverting option is available. Add the suffix -INV to the model number to specify this option. "N" is negative (≈ -70% of the standard value) when this option is installed.

^{3) 60} cm / 2 ft, SMA male to SMA male.

⁴⁾ These devices are generally intended for use with Avtech pulse generators (in pulse mode), and are not characterized for CW operation. An estimate of the upper bandwidth limit may be made from the rated rise time. The lower end of the CW passband may be estimated using the maximum rated

⁵⁾ Do not exceed the rated power dissipation. For pulse mode operation, the power dissipated in R_s is given by $(I_{PULSE}^2 \times R_S \times PW \times PRF) + (I_{DC}^2 \times R_S)$.

⁶⁾ If the diode resistance (dV/dI at lasing) is greater than one-tenth of R_S, R_S should be reduced. Contact a sales engineer for details

⁷⁾ Do not exceed the rated power dissipation. The power dissipated in R_{DC} is given by $(I_{DC}^2 \times R_{DC})$.

GENERAL INFORMATION


INSTALLING THE DEVICE UNDER TEST

The AVX-S1-P1B and AVX-S2-P1B have a "P1B" high-speed socket for pins 8-14 of the diode under test. If the "-T1B" option has been specified, a slide-on socket for pins 1-7 of the diode will also be present.


The "P1B" socket consists of seven high-bandwidth pin sockets. This socket arrangement will accept pins 8-14 of a standard butterfly package with 0.5 mm wide pins. A positive pulse will be applied to the diode anode (pin 10). Pins 8-9 and 11-13 will be grounded.

The optional "T1B" socket consists of a low-bandwidth slide-on socket board for pins 1-7 of a butterfly package. A flexible cable connects the slide-on socket to the output module. A male DB-9 connector is provided on the output module, which provides access to the thermal control pins of the diode. DB-9 pin 2 connects to diode pin 2 (TH). DB-9 pin 3 connects to diode pin 5 (TH). DB-9 pin 4 connects to diode pin 1 (TEC+). DB-9 pin 5 connects to diode pin 14 (TEC-). The remaining DB-9 pins are unconnected. Pins 3, 4, 6, and 7 of the diode are grounded. Access to the photodiode, if present, is not provided. This option is designed for compatibility with Thorlabs temperature controllers and Lumics laser diodes. It may be suitable for others as well.


With no diode installed, the output module will look similar to this:



The diode is first installed by sliding pins 8-14 into the "P1B" pin sockets, as shown below:




If present, the T1B slide-on socket assembly can then be slid onto pins 1-7, as shown below:



To optional third-party TEC controller.

NORMAL TEST ARRANGEMENT

To fully test the instrument, and for normal operation, the output module must be connected as shown below. The basic functional equivalent circuit of the output module is shown.



THERMAL CONTROL (-T1B and -T1D UNITS)

Models with the -T1B or -T1D options include a DB-9 male connector that will mate to third-party temperature controllers. These third-party controller provide a means of controlling the thermoelectric cooler that is typically present in butterfly-packaged laser

diodes, if desired. The need for cooling is dependent on the user's application. Cooling is generally recommended by device manufacturers.


On units with the -T1B option, DB9 connector pins 2 and 3 connect to DUT pins 2 and 5. DUT pins 3 and 4 are grounded.

On units with the -T1D option, DB9 connector pins 2 and 3 connect to DUT pins 3 and 4. DUT pins 2 and 5 are grounded.

SIGNAL CONNECTORS ON THE OUTPUT MODULE

An oscilloscope may be used to monitor the MI and MV outputs. A forward DC bias may be applied to the laser diode by connecting a DC potential of 0 to +10 Volts to the DC solder terminal. The application of a small forward bias often yields a more ideal diode current waveform (as observed on the MI port).

Note that the DC port must be shorted to ground if a bias is not applied. Waveform distortions will occur otherwise.



AVX-S1-P1B OUTPUT MODULE, CONNECTOR VIEW

AMPLITUDE CONTROL

The pulse current through the diode load installed in the output module is given by:

$$I_{DIODE} = (V_{SET} - V_{DIODE}) / R_{S}$$

where V_{SET} is the amplitude setting on the pulser, V_{DIODE} is the forward voltage drop across the diode (typically 2 or 3V), and R_{S} is 50 Ohms on standard units (33 Ohms on units with the -RS33 option).

Standard AVX-S1-P1B models require a positive pulse ($V_{SET} > 0$) on the input, in order to forward bias the device anode.

-INV OPTION

Models with the -INV option have a polarity inverting transformer on the input. This is useful if the user has a pulse generator that generates negative amplitudes only. (The standard AVX-S1-P1B requires a positive pulse for normal operation.)

The amplitude control equation becomes:

$$I_{DIODE} = (-V_{SET} - V_{DIODE}) / R_{S}$$

COMPATIBLE PULSE GENERATORS

The AVX-S1-P1B and AVX-S2-P1B are designed for use with high-speed Avtech pulse generators, such as those the in the AVP, AVPP, AVMP, AVMM, AVMR, AVN, and other families. The AVX-S1-P1B and AVX-S2-P1B may also be suitable for use with other pulse generators. Contact Avtech (info@avtechpulse.com) if you need assistance selecting a pulse generator.

Models in the Avtech AVO-9 series include a pulse generator and an AVX-S series output module in a complete "bundle". See http://www.avtechpulse.com/laser/ for details.

PERFORMANCE CHECKSHEET